



More information on the website
radwag.com/en/info,w1,MV0

MA 200/1.X7.A.WH Moisture Analyzer



MA 200/1.X7.A.WH Moisture Analyzer

The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Statistics



IR sensors



GLP Procedures



Replaceable unit



Statistical Quality Control



ALIBI Memory



Drying modes



Samples drying



Moisture content
analysis



Dry mass determination



Wi-Fi

Datasheet

MA 200/1.X7.A.WH Moisture Analyzer	
Metrological parameters	
Maximum capacity [Max]	200 g
Readability [d]	0,1 mg
Tare range	-200 g
Adjustment	external
Maximum sample weight	200 g
Heating module	halogen
Moisture content repeatability	+/-0,05% (sample ~ 2g), +/-0,01% (sample ~ 10g)
Moisture content readability	0,0001%
Drying temperature range	Max 250 °C
Physical parameters	
Leveling system	manual
Display	7" touchscreen
Weighing chamber	automatic
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions	476×381×346 mm
Net weight	5,2 kg
Gross weight	6,7 kg
Construction	
Protection class	IP 43
Features of use	
Display mode	%MC, %DC, %ATRO MC, %ATRO DC, g, g/kg MC, g/kg DC, -%MC
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
Communication interface	
Communication interface	RS232 ¹ , USB-A, USB-B, Ethernet, Wi-Fi
Electrical parameters	
Power supply	100V – 120V AC 50/60Hz or 200V-240V AC 50/60Hz
Power consumption	6 W
Heating module power	450 W
Environmental conditions	
Operating temperature	+10 ÷ +40 °C
SOP – metrological tests	
Mass indication control	External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer)
Internal adjustment	For .IC models only, GLP report
External adjustment	For all models, GLP report
Drying temperature control	One- or two-point, depending on the drying profile (equipment: GT105k-12/Z Control Thermometer)
Moisture content indication control	Certified MV Test Set
Adjustment	
Internal / External adjustment	Depending on the type of moisture analyzer, GLP report

¹ Barcode scanners, available as weighing instrument accessory, communicate with the instrument via RS232 interface exclusively.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

Antivibration Tables
Moisture analyzer accessories
Barcode scanners
Receipt Printer
Protective cover for balances

RS 232, RS 485 cables
Additional modules
RS 232 cables (scale - printer)
RS 232 – RS 485 Converter

Software

RAD-KEY
Alibi Reader
RADWAG Development Studio

E2R System
Scales Editor 2.1

Device dimensions

MA 200/1.X7.A.WH Moisture Analyzer

